


<b>1.44 MB FDU</b>	<b>Y-E DATA YD-702D-6537D</b>	<b>SA450</b>
--------------------	-------------------------------	--------------



**Note:** This drive is available in two versions: with and without front panel

JUMP.	FUNCTION	COND.
IF	Selects the capacity	
	Mode 2 (2.0/1.0 MB) Automatic Switching operation 2.0 MB: if a high density disk is used 1.0 MB: if a double density disk is used	OFF *
	Mode 3 (2.0/1.6/1.0 MB) Automatic Switching with "Mode Select" operation 2.0 MB: if a high density disk is used with "Mode Select" high 1.6 MB: if a high density disk is used with "Mode Select" low 1.0 MB: if a double density disk is used; "Mode Select" is not used	ON
H2	Selects the output of the "High Density" signal	
	The High Density signal is applied to interface connector pin 2	ON
	The High Density signal is not applied to the interface connector	OFF *
DS1	Drive selected as DRIVE 1	ON *
DS0	Drive selected as DRIVE 0	OFF

<b>1.44 MB FDU</b>	<b>PANASONIC JU-257A 746P</b>	<b>SA450</b>
--------------------	-------------------------------	--------------

**Note:** This drive is available in two versions: with or without front panel.

There are no jumper settings to be made on this drive and consequently there are no jumpers present. The Density Mode and Drive Select parameters cannot be changed and are factory-set by Panasonic.